



# Product Termination Notification

Dc165

PTN TRACKING NR : PTN\_SSR-3821

|                                                  |                                                                                                                                                                                                                                                                 |
|--------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>PRODUCT GROUP</b>                             | <b>SSR – Solid State Relays</b>                                                                                                                                                                                                                                 |
| <b>DESCRIPTION OF CHANGE</b>                     | Last time buy notice for our SGB, SGT, SIT, SVT and SWT 1st generation.                                                                                                                                                                                         |
| <b>CLASSIFICATION OF CHANGE</b>                  | Major (PTN)                                                                                                                                                                                                                                                     |
| <b>REASON FOR CHANGE</b>                         | Due to parts shortages and the availability of next generation, more feature-rich products supplied by celduc relais, we are announcing a last time buy for our SGB, SGT, SIT, SVT and SWT 1st generation.                                                      |
| <b>EXPECTED INFLUENCE ON QUALITY/RELIABILITY</b> | Product Obsolescence Information. One to one replacement part is not always 100% possible but we suggest in this document the best fit replacement.<br>Last Time Buy Deadline and Final Ship Date mentioned in this document are to be taken into consideration |
| <b>PRODUCT CATEGORY</b>                          | 3-phase Solid State Relays 1st Generation                                                                                                                                                                                                                       |
| <b>PART NUMBERS/SERIES/FAMILIES AFFECTED</b>     | Products Impacted and Best Fit Replacements :                                                                                                                                                                                                                   |

| Last Time Buy Product | Best Fit Replacement Product | Best Fit Availability |
|-----------------------|------------------------------|-----------------------|
| SGB942360E            | SGB8850200                   | Available Now         |
| SGB943360E            | SGB8850200                   | Available Now         |
| SGB945360E            | SGB8850200                   | Available Now         |
| SGB947360E            | SGB8890200                   | Available Now         |
| SGB963360E            | SGB8850200                   | Available Now         |
| SGB965360E            | SGB8850200                   | Available Now         |
| SGB967360E            | SGB8890200                   | Available Now         |
| SGT767470E            | SGT7690500                   | Available Now         |
| SGT769390E            | SGT7690500                   | Available Now         |
| SGT865470E            | SGT8850200                   | Available Now         |
| SGT867350*            | SGT8670500                   | Available Now         |
| SGT942360E            | SGT9424300                   | Available Now         |
| SGT944360E            | SGT9444300                   | Available Now         |
| SGT945360E            | SGT9454300                   | Available Now         |
| SGT947360E            | SGT9474300                   | Available Now         |
| SGT948360E            | SGT9694300                   | Available Now         |
| SGT962360*            | SGT9834300                   | Available Now         |
| SGT962360E            | SGT9834300                   | Available Now         |
| SGT965360*            | SGT9854300                   | Available Now         |
| SGT965360E            | SGT9854300                   | Available Now         |

|                         |                                 |                                                  |  |               |
|-------------------------|---------------------------------|--------------------------------------------------|--|---------------|
| Indice de révision : 00 | Date de validation : 08/10/2021 | Lieu de diffusion : Système documentaire Qualité |  | Page N° : 1/3 |
|-------------------------|---------------------------------|--------------------------------------------------|--|---------------|

|                   |                                      |               |
|-------------------|--------------------------------------|---------------|
| <b>SGT96536H*</b> | SGT9854300                           | Available Now |
| <b>SGT965960*</b> | SGT8658500 / SGT8858200 / SGT8859200 | Available Now |
| <b>SGT967360*</b> | SGT9874300                           | Available Now |
| <b>SGT967360E</b> | SGT9874300                           | Available Now |
| <b>SGT967760E</b> | SGT8678500                           | Available Now |
| <b>SGT967960E</b> | SGT8678500 / SGT8879200              | Available Now |
| <b>SGT968360E</b> | SGT8690500 / SGT9694300              | Available Now |
| <b>SIT865390</b>  | SGT8658502                           | Available Now |
| <b>SIT865570</b>  | SGT9654302                           | Available Now |
| <b>SIT865990</b>  | SGT8658502                           | Available Now |
| <b>SIT867570</b>  | SGT9874300+WF115000                  | Available Now |
| <b>SVT764394*</b> | SGT7650500                           | Available Now |
| <b>SVT861394*</b> | SGT8850200                           | Available Now |
| <b>SVT864374*</b> | SGT8850200                           | Available Now |
| <b>SVT864394E</b> | SGT8850200                           | Available Now |
| <b>SVT864994*</b> | SGT8658500                           | Available Now |
| <b>SVT867394*</b> | SGT8670500                           | Available Now |
| <b>SVT867994*</b> | SGT8678500                           | Available Now |
| <b>SVT868394*</b> | SGT8690500                           | Available Now |
| <b>SVT868394E</b> | SGT8690500                           | Available Now |
| <b>SVT868994*</b> | SGT8698500                           | Available Now |
| <b>SVT869394*</b> | SGT8690500                           | Available Now |
| <b>SVT869994*</b> | SGT8698500                           | Available Now |
| <b>SVT965360*</b> | SGT9854300 / SGT9654300              | Available Now |
| <b>SVT965460E</b> | SGT9854300 / SGT9654300              | Available Now |
| <b>SVT965760*</b> | SGT8858200                           | Available Now |
| <b>SVT965760E</b> | SGT8858200                           | Available Now |
| <b>SVT965960E</b> | SGT8859200                           | Available Now |
| <b>SVT967360*</b> | SGT9874300                           | Available Now |
| <b>SVT967360E</b> | SGT9874300                           | Available Now |
| <b>SVT967960*</b> | SGT8879200                           | Available Now |
| <b>SWT860330</b>  | SMT8628521                           | Available Now |
| <b>SWT861730</b>  | SGT8698503                           | Available Now |
| <b>SWT861790</b>  | SGT8698503                           | Available Now |
| <b>SWT862030</b>  | SGT8698503                           | Available Now |
| <b>SWT862090</b>  | SGT8698503                           | Available Now |
| <b>SWT865080</b>  | SGT8698504                           | Available Now |

The above suggested replacement are the Best Fit Replacements but, prior to the installation, technical data-sheets should be consulted on [www.e-catalogue.celduc-relais.com](http://www.e-catalogue.celduc-relais.com) to validate the replacement. On request, celduc can provide you with the detailed differences between 1<sup>st</sup> generation and 2<sup>nd</sup> generation.

\*These products are with 40mm spacing fixing holes housing and suggested best fit replacements are with 47.6mm spacing fixing holes housing. It means you will need to change the fixing holes positions on your heatsink. Consult celduc.



# Product Termination Notification

Dc165

PTN TRACKING NR : PTN\_SSR-3821

| TIME SCHEDULE           |                                                                                                                                                                                                                  |
|-------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Start Shipment date     | N/A                                                                                                                                                                                                              |
| Last Time Buy Date      | We are accepting orders for last time buy products on a first come, first serve basis, <b>up to the 31st of December 2021</b> . After this date, we may not be able to guarantee availability of these products. |
| Last Time Shipment Date | Order placed in compliance with above date must be scheduled for delivery from celduc relais <b>prior to 30/06/2022</b> .                                                                                        |
| SAMPLE AVAILABILITY     | N/A                                                                                                                                                                                                              |
| PRODUCT IDENTIFICATION  | See list of products Impacted                                                                                                                                                                                    |
| QUALIFICATION DATA      | N/A                                                                                                                                                                                                              |
| PRODUCT(S) REPLACEMENT  | See list of Best Fit replacements                                                                                                                                                                                |

celduc relais appreciates and values your business relationship and looks forward to your continued interest in its products.

While we regret any inconvenience this announcement may cause, we are eager to supply your future product requirements with our world class quality product lines. If you have any questions, please call your sales representative.

Thank you for your attention in this matter.

| Issued by                                                                                              | Quality Manager:                                                                                         | Contact information :                                                                                                           |
|--------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| <b>André Trybus</b><br><a href="mailto:atrybus@celduc.com">atrybus@celduc.com</a><br>+33 4 77 53 90 20 | <b>David Conoir</b><br><a href="mailto:d.conoir@celduc.com">d.conoir@celduc.com</a><br>+33 4 77 53 90 20 | <b>celduc relais</b><br>5 RUE AMPERE, 42290 SORBIERS FRANCE<br><a href="http://www.celduc-relais.com">www.celduc-relais.com</a> |

|                         |                                 |                                                     |  |               |
|-------------------------|---------------------------------|-----------------------------------------------------|--|---------------|
| Indice de révision : 00 | Date de validation : 08/10/2021 | Lieu de diffusion :<br>Système documentaire Qualité |  | Page N° : 3/3 |
|-------------------------|---------------------------------|-----------------------------------------------------|--|---------------|